

GOAL ZERO NOMAD[®] 28 PLUS SOLAR PANEL

Big Power, Small Footprint

A foldable, 28 watt panel composed of 4 highly efficient monocrystalline panels in an easy-to-pack form. Power phones and tablets directly from the sun through a built-in, intelligent 2.4A USB port.

Waterproof and Modular

Rugged, waterproof construction means power without worry. Removable kickstand provides optimum angle placement toward sun.

Chainable for Faster Recharge Times

Easily chainable with other Goal Zero Nomad Solar Panels to collect more power from the sun; no extra cables needed.

Charge Goal Zero Power Packs and Power Stations

Features built-in cables, ideal for charging large Goal Zero Power Packs and Power Stations.



SKU# 11805
UPC# 847974005156

Charge the following:	Approximate Charge Time:
GOAL ZERO Switch 10/ Flip 10	2.5-3 hrs
GOAL ZERO Flip 20	4-5 hrs
GOAL ZERO Flip 30	5-8 hrs
GOAL ZERO Venture 30	5-8 hrs
GOAL ZERO Sherpa 50	4-8 hrs
GOAL ZERO Sherpa 100	7-14 hrs
GOAL ZERO Yeti 400	29-57 hrs
Solar Panel:	
Rated Power	28W
Open Circuit Voltage (Voc)	18-22V
Cell Type	Monocrystalline

Ports:	
8.0mm	14-22V, up to 2A (28W max)
USB port	5V, up to 2.4 A (12W max)
General:	
Weight (with leg)	3.0 lbs (1360 g)
Weight (without leg)	2.5 lbs (1134g)
Dimensions (unfolded)	12.1 x 31.6 x 0.1 in (31 x 80 x 0.2 cm)
Dimensions (folded)	12.1 x 7.9 x 1 in (31 x 20 x 2.5 cm)
Certs:	CE
Warranty	12 months