

- Product Data Sheet -



Article **Competition 2AA COB-LED - Flashlight**

Art. number	LX0HYA2AA	Color	Red/ Black	Recom. Retail Price	16,95 €
Manufacturer	LiteXpress	Material	Aluminum/ Rubber		



Description: Work light or flashlight? Whether in the toolbox or in hiking backpack. This competition flashlight by LiteXpress feels equally comfortable everywhere. It has two light sources: A precise, forward-looking LED and a grip-mounted, arealuminating C.O.B for the work use supported by the strong magnet in the end cap. The hands remain free if necessary. With up to 180 m of light range, 18 hours of light duration and 130 lumens you are well supplied in most situations. The lamp has a sturdy aluminum / plastic / rubber housing in the colors red / black, is splash-proof and comes with a hand strap and 2 AA alkaline batteries.

Features - Insulation Products

Insulation effect		Sealing		Capacity	
Cold in hours	n/a	Type of lid	n/a	Capacity in liters	n/a
Hot in hours	n/a	Filling hole in cm	n/a		

Specials

Features - Flashlights

Battery/Rech. Battery		Brightness		Other	
Type	AA	Max lumens	130	Light source	LED
Amount required	2	Min lumens	40	Amount of modes	3
Weight battery in gr	23,00			Modes / functions	High, Low, Quick Flashing
Total weight in gr	46,00	Luminous range			
Batteries included?	no	Max meters	180	Special features	
		Min meters	130		
		Lighting duration			
		Max ¹ h	14,0		
		Min ¹ h	18,0		

¹ Max relates to the lighting duration in highest light mode and Min to the duration in lowest light mode

Dimensions / Others

Inner Carton		Product		Other	
Length in cm	15,20	Length in cm	4,80	Country of Origin	China
Width in cm	18,30	Width in cm	4,80	Customs tariff num.	8513100000
Height in cm	25,60	Height in cm	16,40	EAN13 number	4895168100671
Weight in gr	1.360,00	Diameter	-		
Units	6	Weight in gr	128,00		
Outer Carton		Product packaging		Information - Multitools / Knives	
Length in cm	31,30	Length in cm	4,00	Total length in cm	n/a
Width in cm	38,00	Width in cm	13,50	Handle length in cm	n/a
Height in cm	53,80	Height in cm	24,50	Blade length in cm	n/a
Weight in gr	12.320,00	Weight in gr	213,00	Tools included	n/a
Units	48	Units	1		