

Product Code:

LPT1760CS-HS-12-4.0-15-1



Picture:

Specification:

Rated Voltage	(Vp-p)	12
Max Input Voltage	(Vp-p)	30
*Rated Current	(mA)	≤12
Capacitance at 100Hz	(pF)	15000±30%
*Sound Output at 10cm	(dB)	≥90
Resonance Frequency	(KHz)	4.0±0.5
Operating Temperature	(°C)	-30~+85
Storage Temperature	(°C)	-40~+90
Weight	(g)	1.6
Housing Material		PPS
RoHS		Yes
MSL(Moisture Sensitivity Level)		5a(≤30°C/60% RH 24H F _{bor} life)

*Value applying at rated voltage , 4.0KHz, 1/2 duty , square wave

Test Basic State: Temp(20±2°C),Humidity(40~70%RH),Air pressure(860~1060hPa).

Frequency Response:

Dimensions (UNIT: mm)

Tolerance: ±0.5mm Except Specified

