


Data Sheet


Terminal Blocks with wire protector, 1.5 mm²



NO POSN	DIM A
2	14.2±0.3
3	22.4±0.3
4	30.6±0.5
5	38.8±0.5
6	47.0±0.5
7	55.2±0.7
8	63.4±0.7
9	71.6±0.7
10	79.8±0.7
11	88.0±1.0
12	96.2±1.0

ALL DIMENSION IN MM UNLESS OTHERWISE STATED : 0.= ±0.2mm 00.= ±0.4mm

Housing Material : Polyamide 66 (PA66), Nature flame-retardant to UL 94V-2
 Voltage : 300V (UL), 450V (VDE)
 Current : 20A (UL), 17.5A (VDE)
 Working Temperature : T110 (IEC), 105° C (UL)
 Terminal Body : Brass, nickel-plated
 Wire Protector : Stainless spring steel
 Screws : M2.6x5, Steel zinc-plated
 Wire Range : 0.75 ~ 1.5mm² #22 ~ #12 Sol./Str.

 金筆企業股份有限公司 HEAVY POWER CO., LTD.	
TITLE : TERMINAL BLOCK Model No. PA8 Part No. PA8HDS	
Drawn By	Rev.
yao 2014.12.26	A1

Voltage : 450 V
 Ampere : 17.5 A