



KEYPAD 16 KEYS METAL

Item no. 1565089


Features:

- » Maximum rating: $\geq 24 \text{ V/DC}$, 5 mA
- » Contact resistance: $\leq 100 \Omega$
- » Insulation resistance: $\geq 250 \text{ M}\Omega$
- » Bounce time: max. 3 sec
- » The key "5" has a small convex dot for blind people to identify it.
- » Stroke time: > 1 ms
- » Operation temperature: -40 to +60 °C
- » Electroplating standard:

- Nickel	10 – 15 μ
- Brass	10 – 15 μ
- Chrome	0.2 – 0.5 μ

- » Salt spray test: 48 – 96 hours

Dimensions:






KEYPAD 16 KEYS METAL

Item no. 1565089

Output pins:



e.g. the button "5" is pressed:

Pins	1	2	3	4	5	6	7	8
Ouput	0	1	0	1	0	0	0	0