



Data Sheet

Conductive Copper Foil Tape, 25mm x 10M



Length : 10 m

Width : 25 mm



Picture similar. Please refer to technical data.

Specification

Backing	: Copper
Adhesive	: Conductive Acrylic
Backing thickness	: 0.025±0.005mm
Adhesive thickness	: 0.035±0.005mm
Total thickness	: 0.06± 0.01mm
Color	: Copper

Technical Data

Electrical Resistance	:0.03~0.05ohm
Adhesive power	:1.5kg/25mm
Tensile strength	:>45N/25mm
Ball tack	:#11
Holding power	:1.5kg/25mm
180° peel strength	:15N/25mm
Operating temperature	:-20°C ~ 120°C
Apply temperature	:+10°C ~ 40°C
Storage temperature	:10 ~ 20°C
Storage humidity	:55~65%RH