



Piezo Buzzer (wire)



Lead wire: UL1007AWG26 L1: 150 ± 10mm L2: 5.0 ± 2 mm



Operating Temperature:	-20°C to +60°C
Storage Temperature:	-30°C to +70°C
Operating Voltage:	4 to 28 Vdc
Case Material:	ABS
Sound Pressure Level:	100 dB min