



## Fuse Holder with open & tinned wire

|                       |                       |   |
|-----------------------|-----------------------|---|
| Rating                | 5A 250V AC            | <p style="text-align: center;"><b>Circuit Diagram</b></p>  |
| Insulation Resistance | DC 500V 100M ohm Min. |   |
| Dielectric Strength   | AC 1500V 1 minute     |   |
| Fuse Size             | ø5.0*20mm             |   |

Material:  
 Body: PP  
 Terminal: tin plated brass



Unit: mm