

FLASH



1280x
720p
Video

5 MP
Sensor

12 MP
max.
Resolution

4x
Digital
Zoom

Motion
Jpg
Compression

AV
Out

SD/SDHC
Card
up to
8GB



Sensor	5 MegaPixels CMOS
Display	6.9cm (2.7") TFT Color LCD
Focus range	150cm ~ Infinity
Aperture	F3.2, Fixed Focus
Shutter	Electronic Shutter: 1/2 ~ 1/1024 sec
Resolution	Still Image 12MP (4000x3000) by interpolation, 5MP (2592x1944), 3MP (2048x1536), 1.3MP (1280x960), VGA (640x480) Video: 1280x720, 720x480, 640x480, 320x240
Sensitivity	Auto
White balance	Auto / Daylight / Tungsten / Fluorescent / Cloudy
Exposure control	-2EV to +2EV in 0.3 Step
Burst	Included
Photo effect	Normal / B&W / Sepia / Negative / Red / Green / Blue
Self-timer	2 / 10 seconds.
Storage	External Memory: SD / MMC / SDHC Memory Card Supported Up to 8GB
TV system	NTSC / PAL
File formats	JPG / AVI
Power Supply	2x AA Alkaline Batteries
Ambient temp.	Operating: 0° C to 40° C Storage: -20 to 60° C
Microphone	Built-in
Speaker	Built-in
Dimension	Camera Body: 4.43" x 2.2" x 2.13"
Weight	Camera Body w/o battery: 0.42 lbs

Accessories

- User Manual
- USB / AV Cable
- Pouch
- Strap
- 2x AA Alkaline Batteries
- Software CD

