



Working Temperature: -20°C ~ 60°C  
Working Voltage: DC 5V ~ 24V  
Working Current: 28mA ~ 40mA  
Remote distance: approximately 20 Meters  
Product size: 85mm \* 45mm \* 22mm  
Product weight: 40g  
Certificates: CE, RoHS

Support: WS2801/WS2811/IPD8806/APA102/TM1804/UCS1903/UCS9812

Max 2048 Pixels

## Features:

1. App Control via Bluetooth 4.0, long Control distance, convenient to use
2. Support almost every kind of on-wire or two-wire LED driver IC
3. Brightness adjustable, with 200 kinds of patterns, which are vivid and beautiful
4. Support setting total pixel number, able to control up to 2048 pixels
5. DC 5V ~ 24V wide working voltage, preventing reverse connection of power supply
6. User setting saving

## App:

The specialized App is available on both iOS and Android OS. (Hardware should support Bluetooth 4.0)

- Apple Device: iPhone 4S | iPhone 5/5S/5C | iPhone 6/6Plus | iPhone 6S/6S Plus, supported iOS 8.0 version or newer
- Android OS version should be Android 4.4. or newer
- Search "Magic-LED" or scan the QR code below to download and install the App:

