



PCB LAYOUT

| Contact | Dlm A | Dlm B | Dlm C | Dlm D | Note |
|---------|-------|-------|-------|-------|----------|
| 24 | 30.48 | 27.94 | 15.24 | 17.78 | with Bar |

RoHS compliant

NOTES:

MATERIAL

- 1.Pin(outer sleeve): Brass, machined CuZn
- 2.Plating(outer sleeve): 2um/80u"nickel, Gc
- 3.Insulator Material: Glass filled PBT(UL94V

ELECTRICAL

- 1.Current Rating: 3Amps/contact max.
- 2.Contact Resistance: 4mΩ/contact max.
- 3.Insulation Resistance: ≥10000MΩ at 500V
- 4.Voltage Rating: 100 VRMS/150VDC

MECHANICAL

- 1.Operation Temperature: -55°C to +105°C
- 2.Soldering temperature: +220°C,10s max.

Packing: Tube