




# Rocker Switch (printing 25A12VDC)

規格 Rating	25A 12VDC	裝配孔 Mounting Hole	線路圖 Circuit Diagram
接觸電阻 Contact R	50m ohm Max.		
絕緣電阻 Insulation R	DC 500V 100M ohm Min.		
耐電壓 Dielectric Strength	AC 1500V 1 minute		
使用溫度 Operation Tempature	-20°C ~ 65°C		
動作特性 Circuit	3P SPST ON-OFF With LED indicator		



Unit: mm

Tolerance: ±0.3 except noticed

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.