



Datasheet


Item no. 1587793

V1_0817_01_en

Starter Button Switch (printing 10A24VDC)

Rating	10A 24V DC	Mounting Hole	Circuit diagram
Contact R	50M ohm Min		
Insulation R	DC 1500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 Minute		
Circuit	2P SPST OFF-(ON)		

Material:
Housing: Black, ABS
Button: Black, ABS
Cover: Black, ABS
Screw: Nickel Plated SS41



Unit: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED ±0.3

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE.