

Datasheet

Item no. TC-K10NF2

ceramic capacitor Z5U 10 nF ± 20% 100 V pitch 2.54 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	10 nF
Material	Z5U
Pitch	2.54 mm
Tolerance	± 20%
Type	ceramic
Packaging	bulk

