

Datasheet

Item no. TC-K47NF5

ceramic capacitor Y5V 47 nF -20% to +80% 100 V pitch 5.08 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 100 V
Operating Temperature	-25 °C - 85 °C
Capacitance	47 nF
Material	Y5V
Pitch	5.08 mm
Tolerance	-20% to +80%
Type	ceramic
Packaging	bulk

