

Datasheet

Item no. TC-K68PF500V

ceramic capacitor SL 68 pF ± 10% 500 V pitch 5.08 mm



Specification:

Terminal	THR
Orientation	radial
Operating Voltage	≤ 500 V
Operating Temperature	-25 °C - 85 °C
Capacitance	68 pF
Material	SL
Pitch	5.08 mm
Tolerance	± 10%
Type	ceramic
Packaging	bulk

