

RB-LCD10-2

10.1" IPS Touchscreen Display With Metal Body



The 10" touch display is a durable all-rounder. It is especially characterized by its solid quality. The matt black metal body fits perfectly with the hard coating of the display (H3).

Due to the large number of connections and the built-in speakers, it is suitable as a second monitor for PC and notebook, workshop display, surveillance monitor for camera systems or mobile use in caravans.

It is also suitable for wall mounting due to the drill holes on the back.

MAIN FEATURES

Display	10,1" IPS (25,65cm)
Resolution	1280 x 800 Pixel
Brightness	350 cd/m ²
Contrast	800:1
Viewing Angle	160° - 170°
Colors	16,7M
Operating Temperature	0 - 50°C
Power Supply	12V / 2A

HIGHLIGHTS

Features	Integrated speakers Glare protection Hard coating (3H)
Connections	HDMI, VGA, AV, BNC, 2x USB
Wall Mounting	VESA compatible (75x75)

ADDITIONAL INFORMATION

Dimensions (footless)	244 x 163 x 32mm
Weight	1,2 kg
Article No.	RB-LCD10-2
EAN	4250236815633
Customs Tariff No.	8473302000

Items Shipped	Display, Adapter board, HDMI-Cable, USB-Cable Type A, USB-Cable Type A-MicroUSB, Power Supply, Spare screws, mounting material, remote control
---------------	--