



**NEW**

**HRA-310BT**

*RETRO STYLE FM RADIO  
WITH BLUETOOTH, AUX-IN*



**128W PMPO**

 **Bluetooth®**



*HRA-310BT/BK*

*HRA-310BT/CR*



**AUDIO  
products**

# HRA-310BT

## RETRO STYLE FM RADIO WITH BLUETOOTH, AUX-IN



### CD PLAYER

Loader type	-
Electronic Shock Protection	-
Compressed audio playback	-
Disc support	-
Auto ID3 tag detection	-
MP3 search by	-
Data rate system	-
Fast forward / reverse	-
Track search	-
Intro scan	-
Random play	-
Repeat track / album	-
Program function	-

### TUNER

Tuner type	Scan
Ranges (band)	FM
RDS system / Radiotext	-
Preset stations	-
Stereo / Mono selector	Mono
Automatic tuning	•
Manual tuning	-

### CASSETTE

Cassette deck	-
Automatic Level Control (ALC)	-
One Touch Recording (OTR)	-
Built-in microphone	-

### AUDIO

Total PMPO Output Power	128 Watt
Nominal Output Power (RMS)	2 x 8 Watt

### THD

Electronic volume control	-
Preset equaliser	-
Space surround sound	-

### USB/SD/MMC

Encoding	-
Playback	-
Copy	-
Delete	-
iPod compatibility	-

### TURNTABLE

R.P.M.	-
Tone Arm Mechanism	-

### GENERAL

Remote control	-
Speaker system	2 speaker
Display / Illumination	- / -
Power supply	9V DC (adapter)
Battery Memory	-
Weight	1,575 Kg
Dimensions	255x145x160(h)mm
Accessories included	AC/DC adapter
Colour Versions	Cream and Gold, Black and Gold

### CONNECT.

Bluetooth	•
USB port	-
Card slot	-
Aux-In	•
Headphones socket	-

### COMMERCIAL

Container load 40'	4094 pcs
Container load 20'	2052 pcs
Shipping carton	6 pcs
Gift Box size	286x178x242(h)
Shipping car. size	549x502x301

### Giftbox EAN code

HRA-310BT/BK	7621800032270
HRA-310BT/CR	7621800032287
Master Carton EAN code	
HRA-310BT/BK	7621800054241
HRA-310BT/CR	7621800054258
Country of origin	P.R.C.