

# HEAVY 15T ALL IN ONE TOUCH-PC IP65

4 GB RAM , 240 GB SSD



## MAIN FEATURES

Display	15 inches (38,1 cm)
Max. Resolution	1024 x 768 Pixel
Response time	6 ms
Brightness	350 cd/m <sup>2</sup>
Hor. Viewing angle	160°
Ver. Viewing angle	140°
Color	black
Weight (net)	4.2 kg
Power Consumption (On)	12.4w

## FURTHER SPECIFICATIONS

Processor	Intel® Atom® E3845
Processor frequency	4x 1.91 GHz
Main memory capacity	4 GB DDR3-RAM
Graphics	Intel HD Graphics
Hard disk	240 GB SSD
Number Gigabit-LAN Port	2x
Number Serial	4x
Number USB Type A 2.0	4x

## FURTHER DETAILS

Article No.	CR-1613429
EAN:	4053199511495
Operating system	excluding
Dimensions (H x W x D)	56 x 355 x 283 mm
service	24 months pickup repair service

Published: