

aquapix® W1627 Ocean



HD
HIGH DEFINITION

10 METERS
WATER
PROOF



- 10m** Waterproof
- 16MP** Max. Resolution
- 8x** Digital Zoom
- 2.7" / 6.8cm** TFT LCD
- HD** Video
- Video** Recording with sound
- Support** microSD Cards up to 32GB
- Web** Cam Function
- Lithium** battery exchangeable

aquapix®
UNDERWATER CAMERAS

Waterproof	Up to 10 meters
Sensor	5MP CMOS sensor
Image resolution	16MP*, 12MP*, 9MP*, 5MP, 3MP, 1.3MP, 0.3MP (*by interpolation)
Video resolution	1280x720p, 640x480p, 320x240p /30fps
Lens	Fixed focus, F 3.0, f=8.15mm
Focus range	Normal: 1.5M ~ infinity, Macro: 20 ~ 50 cm
Shutter speed	Normal: 1/12 sec. - 1/1000 sec
Digital zoom	8x
External memory	Micro SD/SDHC Card support up to 32GB (not included)
Display	6.8 cm (2.7") TFT LCD
ISO	Auto / 100 / 200 / 400
Flash mode	Auto / Force on / Force off / Red-eye reduction
Sharpness	Soft, Normal, Strong
White balance	Auto, Daylight, Cloudy, Fluorescent, Tungsten
Self-timer	2/5/10 sec., 3pcs continuous shoot
Web cam function	Yes
Image stabilization	Yes
Face detection	Yes
Shock resistant	Up to 1 meter
Freezeproof	Up to -10°
Scene mode	Auto, Scenery, Night scene, Night portrait, Portrait, Sports, Party, Beach, High sensitivity, Underwater
File format	JPEG, AVI
Interface	USB 2.0
Power source	500mAh lithium battery (exchangeable)
Dimensions	110 x 68 x 29.5 mm
Weight	132g (without battery and memory card)
System support	Windows 2000 / XP / Vista / Win7 / Win10 / Mac OSX (10.2.6 or higher)

ACCESSORIES

- USB cable
- Pouch
- Hand strap
- Manual
- CD
- Lithium battery

W1627-Y Ocean Yellow
Art. Nr. 10061
EAN 4260041685604

W1627-P Ocean Pink
Art. Nr. 10062
EAN 4260041685628

W1627-I Ocean Iceblue
Art. Nr. 10060
EAN 4260041685611

