



M2R WARRIOR (CW/NW LED)

MOST POWERFUL POCKET-FRIENDLY TACTICAL FLASHLIGHT

MAX OUTPUT



1500 lumens

MAX RUNTIME



25 days

MAX THROW



208 meters



Market Applications

UPC: 6926540912570

Tactical
Self-defense
Outdoor

DESCRIPTION

The M2R is our brand new rechargeable dual switch LED tactical flashlight. This light is equipped with the latest XHP35 HD LED powered by a single high discharge rate 18650 with an output range of 1 to 1,500 lumens. The M2R features a quiet tail switch with minimal noise when being clicked on for tactical purposes. The tail cap of this light can magnetically charge directly through the tail tactical switch. The side switch has a similar operation as the OLIGHT S series flashlights, while the tail switch can be switched between conventional and enhanced tactical operation modes allowing the user to access turbo or strobe with a single click. With its slim head, lanyard hole, and dual direction pocket clip, the M2R is the perfect tactical light to carry with you on any adventure.



Red:
Charging



Green:
Charging Completed



OLIGHT Micro-Dok Compatible(Optional Accessory)
* Directly rechargeable with all conventional 18650 batteries

FEATURES

- Durable metal tail switch design making the M2R rechargeable directly from the switch with the OLIGHT signature USB magnetic charging cable.
- The tail cap uses a quiet tact switch and the side button is pronounced with a braille marking for ease of use in a dark and tactical situation.
- It only takes a single press of the tail cap switch to access the 1,500-lumen turbo or strobe mode for high stress situations.
- Comes with a high capacity and high discharge rate 3500mAh 18650 lithium-ion battery that supports up to 1500 lumens with long runtimes.
- Compatible with all 18650 batteries (with a discharge current over 6A and protection board) and the OLIGHT micro-dok.
- Slim head design, detachable pocket clip for both carry directions, and lanyard hole for an enhanced and comfortable user experience.
- This flashlight can be turned on/off from either the side or the tail switch, making it adaptable to different operational habits.

OUTPUT

ICON	Mode 1	Mode 2	Mode 3	Mode 4	Mode 5	Mode 6
	*1,500±700 lumens	700 lumens	250 lumens	60 lumens	15 lumens	1 lumens
	3±110 minutes	120 minutes	375 minutes	20 hours	70 hours	* 25 days
	208 m					
	10,880 cd					

Note:

- (1) These are tests results retrieved using a fully charged 3500mAh 18650 rechargeable battery which is included for this flashlight.
- (2) Turbo (Mode 1) is the maximum output within three minutes after the flashlight is switched on. It is only reachable when the voltage under load is above 3.7V.

* Turbo (Mode 1) has two possible outputs: 1,500 or 1,000 lumens. When the deep single click is set as strobe setting, it will be 1500 lumens. Or when the deep single click is set as turbo ON/OFF switch setting, it will be 1000 lumens.

LIGHT SOURCE

Cree XHP35 HD CW
 Cree XHP35 HD NW

DIMENSIONS

Length: 5.12 in/130.0mm
Diameter (Head): 1.00 in/25.4mm
Diameter (Body): 0.96 in/24.4mm
Weight: 5.26 oz /149g (including battery)

BODY MATERIAL

6061-T6 Aluminum Alloy (main body)

BATTERY SOURCE

3500mAh 18650 (included)


WARRANTY

OLIGHT's 5 Year warranty
 Visit olightworld.com/warranty

STANDARD ACCESSORIES

Double Direction Stainless Steel Pocket Clip
 10A HDC 3500mAh 18650 Battery
 USB Magnetic Charging Cable
 Lanyard
 Holster

WATERPROOF IPX8



DROP TEST



COMPLIANCE

