

Electronic Siren, 12V/DC,15W, 131 x143 x 142 mm


1. Basic Condition

- 1.1 Rated Voltage: 12 VDC
- 1.2 Operating Voltage: 6~15 VDC
- 1.3 Output Power: 15W
- 1.4 Operating Temperature Range: -20°C~+70°C
- 1.5 Storage Temperature Range: -20°C~+85°C


2. Electrical Characteristics

- 2.1 Sound Press Level: 115±3dB at 100cm / 12VDC
- 2.2 Consumption Current: 350 mA (max. 400 mA)
- 2.3 Coil Impedance: 8Ω±3
- 2.4 Tone Nature: One Tone
- 2.5 Material: ABS Plastic

3. Measuring Method



4. Dimension



5. Product Photo

