

## Electronic Siren IC type, 12V/DC, 20W, 88 x 102.5 x 104.2 mm


### 1. Basic Condition

- 1.1 Rated Voltage: 12 VDC
- 1.2 Operating Voltage: 6~15 VDC
- 1.3 Output Power: 20W
- 1.4 Operating Temperature Range : -20°C~+70°C
- 1.5 Storage Temperature Range: -20°C~+85°C


### 2. Electrical Characteristics

- 2.1 Sound Press Level: 115±3dB at 100cm / 12VDC
- 2.2 Consumption Current: 1,000 mA (max. 1200 mA)
- 2.3 Coil Impedance: 8Ω±3
- 2.4 Tone Nature: One Tone
- 2.5 Material: ABS Plastic

### 3. Measuring Method



### 4. Dimension



### 5. Product Photo

