

# Datasheet

Item no. 1661345


V1\_07262018\_01\_en

## Horn Speaker, 10W, 88 x 102.5 x 104.2 mm

### 1. Specification

- 1.1 Coil Impedance: 8Ω
- 1.2 Input Power: 10W
- 1.3 Frequency Range: 800-5K Hz
- 1.4 Operating Temperature Range: -20°C~+70°C
- 1.5 Storage Temperature Range: -20°C~+85°C
- 1.6 Material: ABS Plastic
- 1.7 Housing Color: Black
- 1.8 Net Weight: about 350g

### 3. Dimension



### 4. Product Photo



Test Voltage (AC)	Sound Pressure level (at 1K Hz, 1W/1M)
9 V	95 dB