

Product information

00 20 12 V05

VDE Screwdriver Set

PlusMinus / Slotted

6 parts

- Attractive sales packaging with Euro standard perforation
- Tools in a plastic deep-drawn tray with transparent lid
- Burnished tip, insulating multi-component handle, VDE-tested
- Dimensions (W x H x D): 170 x 370 x 40 mm



General

Article No.	00 20 12 V05
EAN	4003773082569
Weight	510 g
Dimensions	170 x 35 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Content

98 20 25	1 x Screwdrivers for slotted screws (0,4 x 2,5 x 75 mm) ⚠ 1000V ⚡
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (0,8 x 4 x 100 mm) ⚠ 1000V ⚡
98 24 01 SLS	1 x Screwdriver (Slim) Plus/Minus Phillips® (PH/S 1) ⚠ 1000V ⚡
98 24 02 SLS	1 x Screwdriver (Slim) Plus/Minus Phillips® (PH/S 2) ⚠ 1000V ⚡
98 25 01 SLS	1 x Knipex Screwdriver (Slim) Plus/Minus Pozidriv® (PZ/S1 x 80 mm) ⚠ 1000V ⚡
98 25 02 SLS	1 x Knipex Screwdriver (Slim) Plus/Minus Pozidriv® (PZ/S2 x 100 mm) ⚠ 1000V ⚡

technical change and errors excepted