



Specification:

Material:
 Housing: black polypropylene
 Flammability rating: UL94-HB, UL File No. E216959
 Temperature range: -10°C to +100°C
 Rivets: brass, nickel plated
 Springs: spring steel, nickel plated
 9 Volt snaps: brass, nickel plated
 Spring: spring steel, nickel plated
 Contact resistance: under 50mΩ for +/- contacts per EIA-540J000
 RoHS 2 compliant

Mounting instructions:

Use 2x 56 machine screws or eyelets 0.089in OD by 0.15in flange
 Stimpson GS-3 series or equivalent.
 Also adhesives and double sided tapes work well.

Tolerances	mm (inches)
Decimal	±0.5 (0.020)
Fractional	±0.8 (0.030)
Angular	±3°

