


Four 'D' Cell Holder with Solder Lugs

Order code: **18-0552**



Specification:

Material:

Housing: black polypropylene

Flammability rating: UL94-HB, UL File No. E216959

Temperature range: -10°C to $+100^{\circ}\text{C}$

Rivets: brass, nickel plated

Spring: spring steel, nickel plated

9 volt snaps: brass, nickel plated

Contact resistance: under $50\text{m}\Omega$ for \pm contacts per EIA-540J000

RoHS 2 compliant

Tolerances	mm (inches)
Decimal	± 0.5 (0.020)
Fractional	± 0.8 (0.030)
Angular	$\pm 3^{\circ}$

