

SIVACON, Control panel Empty enclosure, without side panels, according to IEC 62208, IP40, H: 2000 mm, W: 1000 mm, T: 400 mm



| Model  |                                 |
|--|---------------------------------|
| Product brand name                                   | SIVACON                         |
| Product designation                                  | Empty control cabinet enclosure |
| Design of the product                                | according to IEC 62208          |
| Design of the surface                                | Powder-coated                   |
| Design of the product / EMC version                  | No                              |
| Protection class                                     |                                 |
| Protection class IP                                  | IP40                            |
| Operating resource protection class                  | Safety class 1                  |
| Suitability  |                                 |
| Suitability for installation / for metric dimensions | Yes                             |
| <b>Suitability for integration</b>                   |                                 |
| • surface-mounted installation                       | Yes                             |
| • flush mounting                                     | No                              |
| Suitability for use / for outside use                | No                              |
| Appearance   |                                 |
| RAL color number                                     | RAL 7035                        |
| Color  | light grey                      |

## Product details

|  |     |
|--|-----|
| Product component  |     |
| • Ventilation door   | No  |
| • Mounting plate   | Yes |
| • Rear door  | No  |
| • Viewing door   | No  |
| • height-adjustable mounting plate                                     | Yes |
| Product feature / of the enclosure / housing for side-by-side mounting | Yes |

## Number

|                           |   |
|---------------------------|---|
| Number of locking devices | 0 |
| Number of doors           | 2 |

## Mechanical Design

|                        |           |
|------------------------|-----------|
| Height                 | 2 000 mm  |
| Width                  | 1 000 mm  |
| Depth                  | 400 mm    |
| Mounting type          |           |
| • 19-inch installation | No        |
| • floor mounting       | Yes       |
| • wall mounting        | No        |
| Net weight             | 146.32 kg |
| Material               | steel     |

## Certificates

|                          |    |
|--------------------------|----|
| Reference code           |    |
| • acc. to DIN EN 61346-2 | U  |
| • acc. to DIN EN 81346-2 | UC |

| General Product Approval | Declaration of Conformity | Test Certificates | other |
|--------------------------|---------------------------|-------------------|-------|
|--------------------------|---------------------------|-------------------|-------|



[Special Test Certificate](#)

[Miscellaneous](#)

## Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1004-3BR4>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1004-3BR4>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF1004-3BR4](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1004-3BR4)



