

EMC cabinet IP40 HxWxD=1800x 600x 800 for stand-alone installation with side panels, IP40



Figure similar

| Model | |
|------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product brand name | SIVACON |
| Product designation | EMC cubicle |
| Type of installation | stand-alone installation |
| Design of the surface | frames and enclosure parts zinkcor-coated, enclosure parts powder-coated on the outside |
| Design of the product / EMC version | Yes |
| Design of the control cabinet / PC design | No |
| Design of the control cabinet / Console design | No |
| Protection class | |
| Protection class IP | IP40 |
| Suitability for installation | <ul style="list-style-type: none"> • for inch dimensions 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch • for metric dimensions M8 |
| Suitability for use / for outside use | No |
| Appearance | |
| RAL color number | RAL 7032 |

| | |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Color | pebble grey |
| Product component | |
| <ul style="list-style-type: none"> • removable frame • Ventilation door • Mounting plate • Rear door • pitched roof • Viewing door • height-adjustable mounting plate | <ul style="list-style-type: none"> No No No No No No No |
| Number of locking devices | 1 |
| Number of doors | 1 |

| Mechanical Design | |
|----------------------------------------------------------|----------|
| Height | 1 800 mm |
| Width | 600 mm |
| Depth | 800 mm |
| Number of modular height units / for installation height | 34 |
| Mounting type | standing |
| Mounting type / 19-inch installation | Yes |
| Net weight | 110 kg |
| Material | steel |

| Certificates | |
|----------------------------------------------------------------------------|---|
| Reference code | |
| <ul style="list-style-type: none"> • acc. to DIN EN 61346-2 | U |

| | |
|---------------------------------|-------|
| General Product Approval | other |
|---------------------------------|-------|

[Miscellaneous](#)



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=8MF2868-4ES>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF2868-4ES>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MF2868-4ES

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

