

SENTRON, cylindrical fuse link, 10 x 38 mm, 20 A, gPV, Un DC:
1000 V



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse link
General technical data	
Operating class of the fuse link	gPV
Size of the fuse link	10x38 mm
Type of voltage	DC
Current / at AC / rated value	20 A
Supply voltage / at DC	1 000 V
Operating voltage / rated value	1 000 V
Main circuit	
Operating current / Rated value	20 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical
Net weight	10 g
Certificates	

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F
F

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW6007-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW6007-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW6007-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>