




# I1R EOS

TINY RECHARGEABLE LED KEYCHAIN LIGHT

MAX OUTPUT	MAX RUNTIME	MAX THROW
		
<b>130</b> lumens	<b>7</b> hours	<b>54</b> meters

\* These information is for market reference only. Please DO NOT make it public.



## MARKET APPLICATIONS:

Outdoors  
Home

UPC : 6926540925143

## DESCRIPTION





The I1R EOS is a tiny rechargeable LED keychain flashlight with dual output settings ranging from 5 to 130 lumens. It weighs only 12g and has an extraordinarily compact size. The I1R is built from strong aluminum alloy and features a built-in rechargeable Li-ion battery that charges through a Micro-USB port when the light head is unscrewed and removed. The I1R features a high-performance Philips LUXEON TX LED paired with a TIR optic lens producing a soft and balanced beam. Changing outputs (5/130 lumens) is simple just by twisting the light head. The I1R EOS is the perfect daily carry keychain flashlight with high output, convenient charging, and easy mode changing.



## FEATURES

- Lightweight and Tiny. The entire light is slimmer than a pinky finger with the length shorter than a AAA battery and weight at only 0.42 oz/12g.
- Features a high-performance Philips LUXEON TX LED paired with a TIR optic lens producing a soft and balanced beam.
- Rechargeable through a built-in Micro-USB charging port. Fully charged within 1 hour and 15 minutes.
- ON/OFF and output changes are controlled through twisting the flashlight head. Twist it slightly to turn it on at 5 lumens and a bit further for 130 lumens.

## OUTPUT

FL1 STANDARD	MODE 1	MODE 2
	130 lumens	5 lumens
	20 minutes	7 hours
	54 meters	13 meters
	730 <sub>cd</sub>	40 <sub>cd</sub>

\*All data above are test results according to ANSI NEMA FL 1-2009 standards.

## LIGHT SOURCE

Philips LUXEON TX LED

## DIMENSIONS

Length: 1.61in/41mm  
Head Diameter: 0.55in/14mm  
Body Diameter: 0.55in/14mm

## WEIGHT

0.42 oz/12g

## BODY MATERIAL

Aluminum Alloy

## POWERED BY

80mAh 3.7V Li-ion Battery (built-in)

## WARRANTY

Olight's 1 Year Warranty  
Visit: <https://olightworld.com/olight-warranty>

## STANDARD ACCESSORIES

Micro-USB Cable

### WATERPROOF



### DROP TEST



### COMPLIANCE

