


# OLIGHT

## USER MANUAL



i1R EOS

Thank you for purchasing OLIGHT products. Before use, please read the manual carefully!

### PACKAGE CONTENTS

i1R EOS, Micro-USB Cable, User Manual

### SPECIFICATIONS

High	130 lumens	54 m	20 min
Low	5 lumens	13 m	7 h
1.5 m	730cd	IPX8	LUXEON TX
			1.61*0.55 in 41*14 mm
			0.42oz/12 g

### FEATURE:


- Lightweight and Tiny. The entire light is slimmer than a pinky finger with the length shorter than a AAA battery and weight at only 0.42 oz/12g.
- Features a high-performance Philips LUXEON TX LED paired with a TIR optic lens producing a soft and balanced beam.
- Rechargeable through a built-in Micro-USB charging port. Fully charged within 1 hour and 15 minutes.
- ON/OFF and output changes are controlled through twisting the flashlight head. Twist it slightly to turn it on at 5 lumens and a bit further for 130 lumens.

### INSULATING FILM

Before your first use, remove the flashlight from the package, and unscrew the light head.

Remove the insulating film inside the light head before putting the light head back on.

Insulating film





### CHARGING



RED




GREEN




Max time to reach a full charge: 75min

### OPERATION



### WARNING



### EU-DECLARATION OF CONFORMITY



EU-Declaration of Conformity can be found here CE:  
<https://olightworld.com/ec-declaration>

### WARRANTY

**Within 30 days of purchase:** Return to the original seller for repair or replacement.

**Within One year of purchase:** Return to Olight for repair or replacement.

**Battery Warranty:** Olight offers a one year warranty for all rechargeable batteries.

This warranty does not cover normal wear and tear, modifications, misuse, disintegrations, negligence, accidents, improper maintenance, or repair by anyone other than an Authorized retailer or Olight itself.

### USA Customer Support

cs@olightstore.com

### Global Customer Support

Customer-service@olightworld.com

Visit [www.olightworld.com](http://www.olightworld.com) to see our complete product line of portable illumination tools.

### Olight Technology Co., Limited

Address: 5th Floor, Building A2, Fuhai Information Harbor, Fuhai Subdistrict, Bao'an District, Shenzhen, China 518103  
Made In China

V1. 04. 18. 2018  
3.0408.6010.9000



LEARN MORE