

Standard cabinet 8MF6 HxWxD=2200x 800x 400 Installation: Side-by-side non-ventilated, assembled, welded IP40



Figure similar

| Model  |  |
|--|--|
| Product brand name                             | SIVACON  |
| Product designation                            | standard system cubicle                              |
| Type of installation                           | installation as suite                                |
| Design of the surface                          | powder-coated  |
| Design of the product / EMC version            | No   |
| Design of the control cabinet / PC design      | No   |
| Design of the control cabinet / Console design | No   |
| Protection class                               |  |
| Protection class IP                            | IP40   |
| Suitability for installation                   |  |
| • for inch dimensions                          | 10-inch, 17-inch, 19-inch, 21-inch, 23-inch, 24-inch |
| • for metric dimensions                        | M8   |
| Suitability for use / for outside use          | No   |
| Appearance                                     |  |
| RAL color number                               | RAL 7032   |
| Color  | pebble grey  |

|                                    |    |
|------------------------------------|----|
| Product component                  |    |
| • removable frame                  | No |
| • Ventilation door                 | No |
| • Mounting plate                   | No |
| • Rear door                        | No |
| • pitched roof                     | No |
| • Viewing door                     | No |
| • height-adjustable mounting plate | No |
| Number of locking devices          | 1  |
| Number of doors                    | 1  |

| Mechanical Design  |          |
|--|----------|
| Height   | 2 200 mm |
| Width  | 800 mm   |
| Depth  | 400 mm   |
| Number of modular height units / for installation height | 43       |
| Mounting type  | standing |
| Mounting type / 19-inch installation                     | Yes      |
| Net weight   | 135 kg   |
| Material   | steel    |

| Certificates                    |                                  |              |
|---------------------------------|----------------------------------|--------------|
| Reference code                  | U                                |              |
| • acc. to DIN EN 61346-2        |                                  |              |
| <b>General Product Approval</b> | <b>Declaration of Conformity</b> | <b>other</b> |



[Miscellaneous](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF6284-4R>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8MF6284-4R>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8MF6284-4R](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF6284-4R)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

