

Class J fuse link 250 A 600 V time-lag, respect national installation rules!



Model	
Product brand name	SENTRON
Product designation	Cylindrical fuse link
Design of the product	With blade contacts
General technical data	
Operating class of the fuse link	Slow
Size of the fuse link	Class J
Type of voltage	AC
Current / at AC / rated value	250 A
Operating voltage / rated value	600 V
Main circuit	
Operating current / Rated value	250 A
Product details	
Product component / striker	No
Mounting position	Any, preferably vertical
Net weight	720 g
Certificates	

#### Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

#### General Product Approval



#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW4544-2HG>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW4544-2HG>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW4544-2HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4544-2HG)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



