

Class J fuse link 300 A 600 V time-lag, respect national installation rules!



| Model | |
|----------------------------------|--------------------------|
| Product brand name | SETRON |
| Product designation | Cylindrical fuse link |
| Design of the product | With blade contacts |
| General technical data | |
| Operating class of the fuse link | Slow |
| Size of the fuse link | Class J |
| Type of voltage | AC |
| Current / at AC / rated value | 300 A |
| Operating voltage / rated value | 600 V |
| Main circuit | |
| Operating current / Rated value | 300 A |
| Product details | |
| Product component / striker | No |
| Mounting position | Any, preferably vertical |
| Net weight | 720 g |
| Certificates | |

Reference code

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

F

F

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW4550-2HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW4550-2HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4550-2HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



