

# Windows Panel PC Datenblatt ALL\_Tablet\_156W10I3

<b>Size</b>	<b>15.6inch</b>	
<b>Display</b>		
Panel Type	Industrial LCD panel A+ grade	
Aspect Ratio	16:9	
Resolution	1366*768	
Contrast	1000:1	
Luminance	800nit	
Response time	5ms	
Active Area (mm)	342*192	
Display colors	16.7M(8-bit)	
View angle	75/75/75/75	
<b>PC Configuration</b>		
Processor	Intel Core i3 4010UT Dual-core 1.7Ghz (sehr leiser Lüfter)	
Graphic card	Intel HD Graphics 4400	
Memory	4G DDRIII RAM	
Hard disk	32G/64G SSD	
WiFi	Built-in, 802.11a/b/g/n	
Audio	Realtek ALC662 HD Audio decoding controller, Mikrofon über Klinke möglich	
Ethernet	1*Realtek RT8111E LAN chip for 1000Mbps	
Speaker	Inbuilt speaker	
I/O ports	1*12V DC_Jack input 1*VGA 1*HDMI 4*USB2.0 port, 10.1" & 10.4" panel pc only have 2*USB2.0 port 1*RJ-45 network interface 1*Audio I/O interface 2*com(Serial port)	
Operation Temperature	-10°C-50°C	
Storage Temperature	-10°C-60°C	
Operation Humidity	10%--80%	
Storage Humidity	10%-90%	
Certificate of Approval	CE,CCC,ISO,FCC,ROHS	
Installation method	Embedded, Wall Mount, Desktop <b>(optional)</b>	
Touch Screen	10-point Projected capacitive touch screen with tempered glass	
Color	Silver, black color <b>(optional)</b>	
Bezel thickness	3mm Aluminum bezel	
IP rating	IP65 dustproof and waterproof for front panel	
Operating System	Windows10 Pro Original Version with License	
Material	Aluminum alloy enclosure	
Package	EPE+Carton	
<b>Operating System</b>	OS,Original version Windows 7/8.1/10 OS with license label <b>(optional)</b>	



## ▶ I/O of Panel PC



WIFI



DC



VGA



HDMI



USBx4



LAN



Audio



COM



COM