



VGA Monitor Cable M/M, 2m

Part No.: 37820

Description

- Gold Plated 15 Way HD Male to 15 Way HD Male
- Designed for highest quality monitor applications, including CAD, DTP and Multimedia installations when preservation of display is a major consideration
- Triple shielded 'low loss' coaxial cable, gold plated contacts and gold plated metal hoods assembled in accordance with 'EMC' compatible construction techniques
- Incorporating secondary internal screening which provides a high degree of EMI shielding with clearer signal transmissions and minimum distortion
- Supports all VGA and SVGA resolutions up to 2048 x 1536 (WQXGA)
- 25 year warranty

Our Premium Gold VGA cables have been designed for users who demand the best possible performance with maximum reliability. No compromises have been made in design or construction to ensure that these cables provide superb picture quality at the highest resolutions, even over very long distances.

Why choose LINDY Premium Gold VGA Cables

Available in Male to Male and Male to Female configurations, our Premium Gold VGA cables range in lengths from 0.5m to 100m. All are backed by our 25 year warranty. They're the perfect choice for high quality, professional presentation, CAD, DTP and AV installations.