



Bi-directional HDMI 1.4 10.2G Switch

Part No.: 38036

Description

- Dual-purpose - Connect two sources to one display and switch between them
- Alternatively, connect one source to two displays and switch to show the signal on one OR the other
- Supports resolutions up to 4K@30hz 4:4:4 8bit
- No external power supply required
- 2 year warranty

The Lindy Bi-Directional HDMI switch allows the user to plug two HDMI source devices into a single 4K Ultra HD TV or projector, then switch between them using a push button on the unit. Alternatively, plug one high definition source in to two 4K TVs or projectors, then switch to show the image on either of the screens. The switch's compact design means it can also be easily hidden away and takes up almost no desk or stand space.

This bi-directional switch is ideal for use with HDMI source devices such as Blu-Ray players, set top boxes or media players, and great for increasing a displays number of HDMI ports, while also avoiding the task of constantly unplugging and re-plugging in HDMI cables. This switch is also useful for splitting a source to 2 different displays but only requiring one display to be switched on at one time. Support for resolutions up to 4K@30Hz 4:4:4 ensures video can be seen be seen with greater clarity, perfect for use in residential installations or small scale collaboration scenarios.

Technical details

Specifications

- AV Interface: HDMI
- Interface Standard: HDMI 1.4
- Supports Bandwidth: 10.2Gbps
- Maximum Resolution: 4096x2160@30Hz 4:4:4 8bit
- HDCP Support: Pass-through

- Supported Audio: Pass-through
- Separate Audio Ports: -
- IR Support: -
- CEC Support: Pass-through
- Serial Interface: -
- Special Features: -

Connectors

- Input: HDMI Type A (Female) - Bi-directional
- Output: 2 x HDMI Type A (Female) - Bi-directional
- Control: -
- Power: Powered by HDMI Interface

Physical Properties

- Dimensions (approx.) WxDxH: 50x52x20mm (1.97x2.05x0.79in)
- Housing Material: Metal
- Net Weight: 0.073kg (0.16lb)
- Operating Temperature: 0°C - 65°C (32°F - 149°F)
- Storage Temperature: 0°C - 90°C (32°F - 194°F)
- Humidity: 5 - 30% RH (non-condensing)
- Power Requirements: -
- Colour: Black

Miscellaneous

- Packaging Type: Carton Box
- Packaging Dimensions: 75x30x65mm (2.95x1.18x2.56in)
- Gross Weight: 0.08kg (0.18lb)
- Warranty (Years): 2
- Certificated: CE, FCC, RoHS & REACH

Package content

- Bi-directional HDMI Splitter
- Lindy Manual

Purchasing Information

- No.: 38036
- EAN: 4002888380362