



Mini-DP 1.2/HDMI 4K & VGA Adapter, Active
Part No.: 41070

Description

- Connect your Mini DisplayPort equipped Ultrabook or Surface Pro to a HDMI or VGA display/projector
- Supports resolutions up to 4K Ultra HD 60Hz HDMI, and 1920x1200p VGA
- Compatible with Intel Thunderbolt
- Plug & Play installation, no power supply required
- 2 Year Warranty

Perfect for field based and BYOD applications this Mini DisplayPort/Thunderbolt adapter offers a cost-effective solution for connecting a HDMI or VGA equipped high definition monitor, projector, or LCD screen to a Mini DisplayPort equipped Notebook, Ultrabook, Surface Book or Surface Pro.

With its lightweight, low profile design, the adapter easily fits into a Notebook bag and simply expands your available connectivity options, so you can connect to the most commonly used digital and analogue video equipment, without having to carry multiple adapters. Support for resolutions up to 4K 60Hz Ultra HD (HDMI only) allows you to connect to the very highest resolution displays and projectors, so you will never have to sacrifice picture quality.

Please Note: Only one output channel may be used at a time.

This adapter / converter cable supports iMac / Mac / MacBook Thunderbolt ports.

If you are having trouble with 4K displays please refer to <https://support.apple.com/en-us/HT202856>

Package Contents:

Mini DisplayPort to 4K HDMI / VGA Converter Adapter

Technical details

- Input: Mini DisplayPort Male (Thunderbolt 1/2 Compatible)
- Output: VGA Female & HDMI Female
- Only one output can be used at a time
- Chipset: VGA : ANX9833 // HDMI : PS8339B
- DisplayPort 1.2 Compatible
- Supports Resolutions up to 3840x2160 @ 60Hz (4:2:0 @ 8bpc) – HDMI
- Supports Resolutions up to 1920x1200 @ 60Hz – VGA
- Supports 8/10/12bit colour depths
- Supports HDCP 1.4
- Powered via Mini-DisplayPort, no external PSU port
- Transparent operation no configuration required
- Housing: White ABS Plastic
- Cable Length: Approx. 15cm
- Power Consumption: 700mW
- Operating Temp: 00C ~ +700C
- Working Humidity: 10 ~ 85% RH

© LINDY 2019