

Husky Air

**SEAMLESSLY CONNECT TO YOUR
OUTDOOR PROPERTY.**



With the EZVIZ Husky Air, you always enjoy peace of mind. The ezGuard is an outdoor Wi-Fi camera designed for the outdoor security of your office, your store, your parking or your entrance when you're not there. It is equipped with a built-in strobe light and siren to scare off unwanted intruders. It also has two antennas for maximum Wi-Fi and two-way audio. Thanks to the night vision, you can see what's going on, even at night. Just check the app on your smartphone, wherever you are, whenever you want.



HIGHLIGHTS



HD resolution

Crystal clear images and videos



Night vision up to 30 metres

See what's happening, even in the dark



Active defense

Built-in strobe light and siren



Free local storage

Store on an SD card or recorder



Stable Wi-Fi

Two external antennas



Instant alerts

Your mobile keeps you up-to-date



Two-way audio

Built-in speaker and microphone



Easy to install

Includes a mounting kit for walls and ceilings



Weatherproof, dustproof

Always secure, come rain or shine



Easy-to-use app

Crisp lay-out, user-friendly features

ABOUT EZVIZ


EZVIZ helps you app your life. Right from the palm your hand, you connect visually to your home or your work. Welcome to the smart home and business!

FEATURES



ALWAYS CONNECTED. ALWAYS SAFE

The Husky Air outdoor camera has 24/7 HD live streaming. Check in on your property via the app, whenever you want.




BUILT-IN STROBE LIGHT AND SIREN

The Husky Air is your active line of defense. When an intruder is detected, the camera immediately sends you a notification on your mobile and sets off a bright strobe and a loud siren.



HAPPENING, EVEN IN THE DARK

Even in total darkness you see what's happening. The camera automatically switches to a sharp monochrome video stream when it's dark. Thanks to this night vision, you get clear, detailed images at ranges up to 30 meters. You can check the surroundings of your store, your parking or your garden during the night.




FEATURES



DESIGNED FOR ALL WEATHER

The Husky Air has an IP66 rating. This means it is dust-proof, waterproof and designed to function in the most extreme circumstances or temperatures, from -30°C to 60°C.



LISTEN IN AND TALK

Thanks to the built-in two-way audio, you will not be a mere observer but you are able to interact. Just open the EZVIZ app, start the communication and decide whether you want to scare off an intruder or talk with your colleagues at work or the visitor at your entrance.

ENJOY A STRONG, STABLE CONNECTION

Sometimes, outdoor cameras suffer from a router signal that is too weak. Not so with the Husky Air: it comes with two antennas, ensuring a strong and stable WiFi connection. As a result, you can mount it where you need it most on your outdoor property.




FREE STORAGE

The camera has an integrated micro SD card slot that supports up to 128GB of storage (card not included). You can also store the pictures and videos on the EZVIZ NVR X3 or X3C video recorder.



FEATURES




ALWAYS UP-TO-DATE

Whenever movement is detected, you get an instant notification via the app. You immediately know what's going on.




WHEREVER YOU NEED IT

The Husky Air is easy to install. Thanks to the mounting kit for walls and ceilings you can install it on anywhere you want or need.



INTEGRATED EZVIZ SOLUTION

All EZVIZ Wi-Fi cameras are ready for the smart home. You can for instance connect the Husky Air with your nearby EZVIZ door or window sensors via the A1 Alarm Hub. All-round security at your fingertips.



ONE APP DOES ALL THE WORK

With the easy-to-use EZVIZ app, you can view up to four live video streams at the same time with different smartphones, iPads or even PCs. You can connect all your EZVIZ security devices on one and the same app.

SPECIFICATIONS



CAMERA

Image sensor	1/4" Progressive Scan CMOS
Minimum illumination	0.02 lux @(F2.0, AGC ON), 0 Lux with IR
Shutter	Self-adaptive shutter
Lens	2.8mm @ F2.2, Horizontal angle: 92° Diagonal angle: 108°
Lens Mount	M12
Day & Night	IR cut filter
DNR	3D DNR
WDR	Digital WDR

COMPRESSION

Video Compression	Smart H.264
H.264 Type	Main Profile
Video Bit Rate	HD; balance; and fluency. Adaptive bit rate

IMAGE

Max. Resolution	1280 × 720, support dual-stream
Frame Rate	50Hz @ 25fps, 60Hz @ 30fps; adaptive frame rate of network transmission
Image setting	Brightness, contrast, saturation, etc. (configure via Ezviz studio)
BLC	Support

NETWORK

Storage	Support Micro SD card (Max. 128G)
Smart Alarm	Intelligent motion detection
One-key configuration	SmartConfig (Wi-Fi one-key configuration)
Protocols	Ezviz cloud proprietary protocol
Interface Protocol	Ezviz cloud proprietary protocol
General Function	Flicker filter, dual-stream, heart beat, mirror image, password protection, watermark
Wired network	A RJ45 Ethernet Port, adaptive rate of 10/100M

WIRELESS PARAMETERS

Standard	IEEE802.11 b/g/n
Frequency Range	2.4GHz ~ 2.4835 GHz
Channel Bandwidth	Support 20MHz
Security	64/128-bit WEP, WPA/WPA2, WPA-PSK/WPA2-PSK, WPS
Transmission Rate	11b: 11Mbps, 11g: 54Mbps, 11n: 135Mbps

GENERAL

Operating Conditions	-30°C to 60°C, humidity 95% or less (non-condensing)
Power Supply	C 12V±10%
Power Consumption	8W MAX
IP Grade	IP66
IR Range	Max. 30 meters
Dimensions (mm)	150,44 x 85,80 x 71,64mm
Weight	326 g

What's in the box?

- 1 x EZVIZ Husky Air camera
- 1 x Power adapter
- 1 x Mounting Template
- 1 x Screw Kit
- 1 x Quick Start Guide