



1m DVI-I Single Link Cable, Black Line

Part No.: 36260

Description

- DVI-I cable for home and small office applications
- Supports DVI resolutions up to 1920x1200@60Hz and HDTV resolutions up to 1080p
- Robust PVC housing, nickel connectors, 24K gold plated contacts
- Tripled shielded cable, corrosion resistant tinned copper 30AWG conductors
- 10 year warranty

From the Lines cable connectivity concept developed by Lindy, Black Line DVI-I cables are fully featured, entry level connection solutions, perfect for connecting PCs to monitors or projectors.

Black Line DVI-I cables feature triple shielded construction with 30AWG tinned copper conductors for performance and corrosion resistance. Nickel connectors and 24K gold plated contacts maintain signal integrity and reliability.

The tough PVC housing incorporates an integrated finger grip for easy installation. Large thumb screws allow the connector to be tightened into place without the need for a screwdriver and a flexible strain relief prolongs cable life.

Black Line DVI-I cables support resolutions up to 1920x1200@60Hz including HDTV resolutions up to 1080p. These cables support both analogue and digital transmission.

Black Line DVI-I cables are available in lengths of 0.5m to 5m.

Technical details

Connectors

- Connector A: DVI-I Male (Single Link)
- Connector B: DVI-I Male (Single Link)
- Housing Material: PVC
- Connector Plating: Nickel
- Pin Construction: Brass
- Pin Plating: 24K Gold 1µm
- Dimensions (approx.) WxDxH: 36.8x44.5x12.5mm (1.45x1.75x0.49in)

Cable Construction

- Length: 1m (3.28ft)
- Standard: DVI-I Single Link
- Colour: Black
- Type: Round
- Jack Diameter: 8.0mm (0.32in)
- Jacket Material: PVC
- Conductor Material: Tinned Copper
- Conductor Gauge: 30AWG
- Shielding: Aluminium/Magnesium Braid 85%

Specifications

- Supported Bandwidth: 4.95 Gbps
- Maximum Resolution: 1920x1200@60Hz
- Nominal Attenuation: 1 - 825Mhz < 12db
- Minimum Bend Radius: 120mm (4.72in)
- Operating Temperature: -20°C - 80°C (-4°F - 176°F)
- Storage Temperature: -25°C - 85°C (-13°F - 185°F)

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH, UL

Purchasing Information

- No. 36260
- EAN: 4002888362603

This product is also available in other lengths

- 36261 - 2m (6.56ft)
- 36262 - 3m (9.84ft)
- 36263 - 5m (16.44ft)

© LINDY 2019