



2m CROMO Mini DisplayPort to DisplayPort Cable

Part No.: 36312

Description

- Superior performance and design Mini DisplayPort to DisplayPort cable
- Supports UHD resolutions up to 4K 4096x2160@60Hz 4:4:4 10bit
- Chrome design ABS housing, 24K gold plated connectors and contacts
- Triple shielded cable, corrosion resistant, high performance tinned copper 32AWG conductors
- DisplayPort 1.2, 4K, 3D, 21.6Gbps; 10 year warranty

CROMO Mini DisplayPort To DisplayPort Cables feature triple shielded construction with 32AWG conductors for premium performance and corrosion resistance. High quality 24K gold plated contacts and connectors maintain optimal signal integrity and maximum reliability.

UHD resolutions up to 4K 4096x2160@60Hz 4:4:4 10bit, including stereoscopic 3D, are supported. CROMO DisplayPort cables are capable of delivering 4:4:4 colour spacing for the most accurate colour representation possible.

CROMO cables feature sleek chrome design ABS housing to complement the aesthetics of style focused commercial and home applications.

CROMO Mini DisplayPort to DisplayPort cables are available in lengths: 0.5m, 1m, 2m, 3m and 5m.

Technical details

Connectors

- Connector A: Mini DisplayPort Male

- Connector B: DisplayPort Male
- Housing Material: Chromed plated ABS
- Connector Plating: 24K Gold 3µm
- Pin Construction: Phosphor Bronze
- Pin Plating: 24K Gold 15µm
- Dimensions (approx.) WxDxH:
 - Mini DisplayPort: 10x32x7mm (0.39x1.26x0.28in)
 - DisplayPort: 19.7x38.9x12mm (0.77x1.53x0.47in)

Cable Construction

- Length: 2m (6.56ft)
- Standard: DisplayPort 1.2
- Colour: Grey
- Type: Round
- Jack Diameter: 5.5mm (0.22in)
- Jack Material: PVC
- Conductor Material: Tinned Copper
- Conductor Gauge: 32AWG
- Shielding: Copper Braid 85%

Specifications

- Supported Bandwidth: 21.6Gbps
- Maximum Resolution: 4096x2160@60Hz 4:4:4 10bit
- Nominal Attenuation:
 - 300kHz-825MHz <5dB
 - 825MHz-2.475GHz <5dB
 - 2.475GHz-4.125GHz <12dB
 - 4.125GHz-5.1GHz <20dB
- Minimum Band Radius: 55mm (2.17in)
- Operating Temperature: -20°C - 80°C (-4°F - 176°F)
- Storage Temperature: -25°C - 85°C (-13°F - 185°F)
- ATC Approved: -

Miscellaneous

- Packaging Type: Polybag
- Warranty (Years): 10
- Certificated: RoHS, REACH, UL

Purchasing Information

- No.: 36312
- EAN: 4002888363129

This product is also available in other lengths

- 36310 - 0.5m (1.64ft)
- 36311 - 1m (3.28ft)
- 36312 - 2m (6.56ft)

© LINDY 2019