



## UK Mains Power Cable, 2m

Part No.: 30409

### Description

- Connector A: UK Mains Plug
- Connector B: IEC C5
- Cable type: H05-VVF 3G\*0.75mm<sup>2</sup>
- Colour: Black
- 10 years warranty

LINDY power cables are perfect for use in professional areas (recording studios, light systems and also for event locations of any kind, etc.) – but you can also use them in private sections.

Due to the high temperature resistance from -10 to 70°C during operation these cables can also be used in non air-conditioned areas.

### Technical details

- Number of wires: 3
- Wire cross-section: 0.75mm<sup>2</sup>
- Available lengths: 2m
- Operating temperature: ca. -10 to 70°C
- Storage temperature: ca. -25 to 70°C

Note: Only for use in dry areas!

