


PocketBook Touch HD 3

E-reading without compromise



Device specifications

Display type	E Ink Carta™
Display resolution	1072 × 1448
Display size	6" (15.24 cm)
DPI	300
Colour depth	16 levels of greyscale
Touchscreen	Capacitive (multisensor)
Frontlight	Yes (SMARTlight)
Processor	Dual Core (2×1 GHz)
RAM	512 MB
Internal storage	16 GB*
Battery	1500 mAh (Li-Ion Polymer)**
G-Sensor	Yes
Cover sensor	Yes
Wi-Fi	Yes
Bluetooth	Yes
USB output	Micro USB
Platform (OS)	Linux 3.0.35
E-book formats (without conversion)	PDF, PDF(DRM), EPUB, EPUB(DRM), DJVU, FB2, FB2.ZIP, DOC, DOCX, RTF, PRC, TXT, CHM, HTM, HTML, MOBI, ACSM
Image formats	JPEG, BMP, PNG, TIFF
Audio formats	MP3 (USB audio adapter/Bluetooth)
Audio book formats	MP3, M4B
Text-to-Speech	English (15 additional languages available for free download on pocketbook.ch)
Dictionaries	ABBYY Lingvo® dictionaries (24 language combinations), English - German, Webster's Dictionary 1913
Online services	PocketBook Cloud, ReadRate, Dropbox PocketBook, Send-to-PocketBook
Applications	Book Store, Library, Dictionary, Browser, Audio Books, Audio Player, Gallery, Calculator, Notes, RSS News, Chess, Klondike, Scribble, Sudoku
Dimensions	161.3 x 108 x 8 mm
Weight	155 g
Available colours	Spicy Copper
HZO™ water protection	Yes (IPx7)
Retail set	E-reader, micro USB cable, micro USB audio adapter, quick start guide, warranty card

* The actual available internal storage size may vary depending on the software configuration of your device.

** Up to one month of battery life (may vary depending on usage mode, connectivity and settings).

www.pocketbook.ch

The producer may change the product characteristics, colours and packaging without prior notice. Please check the website www.pocketbook.ch for the latest product information.