

RCBT60T / RECBT60T

12/24v Fully Automatic 60A Battery Charger with SmartCharger Technology

3 Stage SmartCharge technology

Optimises battery performance and improve a batteries ability to hold charge

Includes jump starting function

540A starting current for when a flat battery needs to be revived quickly

Suitable for 12V, 24V and Stop/Start batteries

Will work across mixed battery types in cars to commercial vehicles



LED display shows voltage, current and charge mode selected

Making it easy to select the required charging mode and review charging performance



Specifications

Part number	RCBT60T
Input voltage AC	230v
AC Input power	900w
Charge current	60A (RMS) / 40A (EN)
Start current	540A (RMS)
Cranking cut-off	30 seconds
Charging voltage (12v/24v)	Lead acid 14.5v / 29.0v AGM 14.8v / 29.6v Gel 13.8v / 27.6v
Battery capacity (12v)	20-700Ah
Battery capacity (24v)	20-350Ah
Dimension (LxWxH)	360x375x875mm
Weight	18.5Kg