



Part No	<b>90NB0JR2-M01520</b>
Model Name	<b>UX433FA-A6102T</b>
EAN Code	<b>4718017172295</b>
UPC Code	<b>192876172292</b>
LCD Cover Color & Decoration	<b>Royal Blue Glass (Glare)</b>
Top Case Color & Decoration	<b>Royal Blue Metal</b>
On board processor	<b>Intel® Core™ i7-8565U Processor 1.8 GHz (8M Cache, up to 4.1 GHz)</b>
Operating System	<b>Windows 10 (64bit)</b>
Office	<b>Includes 1 month Trial for New Microsoft Office 365 Customers</b>
Display	<b>14.0'//Ultra Slim 300nits//FHD 1920x1080 16:9//Anti-Glare//NTSC:72%//Wide View</b>
Number Pad	<b>Yes</b>
Chipset	<b>N/A</b>
Memory Slot	<b>N/A</b>
Total System Memory	<b>LPDDR3 8GB</b>
On board memory	<b>LPDDR3 8GB</b>
Memory Max.	<b>8G</b>
Storage	<b>PCIEG3x2 NVME 256G M.2 SSD</b>
EMMC/ISSD	<b>N/A</b>
External video display modes	<b>HDMI 1.4</b>
Discrete/Share	<b>Share</b>
IGPU	<b>Intel UHD Graphics 620</b>
Video memory	<b>N/A</b>
Video Camera	<b>HD IR/RGB Combo Camera</b>
FingerPrint	<b>N/A</b>
On board Wireless	<b>802.11ac+Bluetooth 5.0 (Dual band) 2*2</b>
LAN	<b>N/A</b>
Card Reader	<b>Type: Micro SD</b>
USB Port	<b>1x USB 2.0 1x USB3.1 Type A (Gen1) 1x USB3.1 Type C (Gen 2)</b>
Interface	<b>1x Headphone-out &amp; Audio-in Combo Jack 1x HDMI</b>
Audio	<b>Built-in array microphone harmon/ kardon</b>
Weight (Kg)	<b>0.94 KG (Without Battery) 1.19 KG (with 3 cell battery)</b>
Dimension (cm)	<b>31.9(W) x 19.9(D) x 1.59 ~ 1.59 (H) cm</b>

AC Adapter	<b>ø4.0</b> <b>45W AC Adapter</b> <b>Output: 19V DC, 2.37A, 45W , Input: 100~240V AC</b> <b>50/60Hz universal</b>
Battery	<b>50WHrs, 3S1P, 3-cell Li-ion</b>
Replaceable Battery	<b>No</b>
Keyboard type	<b>Illuminated Chiclet Keyboard</b>
Software	<b>ASUS Live Update</b> <b>ASUS Product Registration Program</b> <b>ASUS GiftBox</b> <b>ASUS Splendid</b> <b>CyberLink PowerDVD 12(JP only)</b>
Security	<b>TPM (Firmware TPM)</b>
Supplied Accessories	<b>Sleeve</b>
Warranty	<b>2 years Carry-In Germany and Austria</b>

