



| | |
|------------------------------|--|
| Part No | 90NB0JV3-M00310 |
| Model Name | UX333FA-A4021T |
| EAN Code | 4718017105286 |
| UPC Code | 192876105283 |
| LCD Cover Color & Decoration | Royal Blue Metal |
| Top Case Color & Decoration | Royal Blue Metal |
| On board processor | Intel® Core™ i5-8265U Processor 1.6 GHz (6M Cache, up to 3.4 GHz) |
| Operating System | Windows 10 (64bit) |
| Office | Includes 1 month Trial for New Microsoft Office 365 Customers |
| Display | 13.3"//Ultra Slim 250nits//FHD 1920x1080 16:9//Glare//NTSC:72%//Wide View |
| Number Pad | N/A |
| Chipset | N/A |
| Memory Slot | N/A |
| Total System Memory | LPDDR3 8GB |
| On board memory | LPDDR3 8GB |
| Memory Max. | 8G |
| Storage | PCIEG3x2 NVME 256G M.2 SSD |
| EMMC/ISSD | N/A |
| External video display modes | HDMI 1.4 |
| Discrete/Share | Share |
| IGPU | Intel UHD Graphics 620 |
| Video memory | N/A |
| Video Camera | HD IR/RGB Combo Camera |
| FingerPrint | N/A |
| On board Wireless | 802.11ac+Bluetooth 5.0 (Dual band) 2*2 |
| LAN | N/A |
| Card Reader | Type: Micro SD |
| USB Port | 1x USB 2.0 1x USB3.1 Type A (Gen1) 1x USB3.1 Type C (Gen 2) |
| Interface | 1x HDMI |
| Audio | Built-in speaker Built-in array microphone Sonic Master harmon/ kardon |
| Weight (Kg) | 0.94 KG (Without Battery) 1.19 KG (with 3 cell battery) |
| Dimension (cm) | 30.2(W) x 18.9(D) x 1.69 ~ 1.69 (H) cm |
| AC Adapter | ø4.0 45W AC Adapter Output: 19V DC, 2.37A, 45W , Input: 100~240V AC 50/60Hz universal |
| Battery | 50WHrs, 3S1P, 3-cell Li-ion |
| Replaceable Battery | No |
| Keyboard type | Illuminated Chiclet Keyboard |
| Software | ASUS Live Update ASUS Product Registration Program ASUS GiftBox ASUS Splendid |
| Security | N/A |
| Supplied Accessories | Sleeve |
| Warranty | 2 years Carry-In Germany and Austria |