

# External SSD Enclosure, M.2 - USB 3.1 Type C



Quick Installation Guide DA-71115 Rev. 2

## **Product Description**

High Speed USB 3.1 Type-C to NGFF (M.2) SSD Storage Case - A perfect solution for data transfer or data backup!

This is a compact NGFF (M.2) SSD Enclosure which will allow you to plug in your NGFF (M.2) SSD and use it as a portable external drive at USB 3.1 speed. Super data transfer rate up to 6Gbps - 10x faster than USB 3.0. By formatting this case with a drawer function, there is now extra protection for your hard drive. Reverse compatible with USB 3.0/2.0 and 1.1, this enclosure is a perfect solution for data transfer or data backup!

### **Features**

- Connects NGFF B Key SSD safely to computer via USB port
- Compliant with SATA 3.0 specification
- Compliant with USB 3.1 specification
- Supports data transfer up to 10 GB/s.
- Supports SATA-based NGFF SSD
- Supports B Key NGFF SSD
- Applicable SSD hard drive:

Support **22\*30mm/42mm/60mm/80mm** 

NGFF (M.2) Interface SSD hard drive

- Supports UASP (USB Attached SCSI Protocol)
- Easy installation & no driver required
- No additional power required
- Support boot function
- Supports Plug & Play and Hot-Swapping
- Support System: Windows XP/Vista/Windows7/8/8.1/10/Linux/MAC
  Free drive with USB

Please note that it supports SATA-based B Key SSD only. It does NOT support PCI-E based B key & any M key SSD.

## **Package Content:**

- External SSD Enclosure, M.2 USB 3.1 Type C
- USB cable (C A), 45 cm
- Screwdriver + screws
- User manual
- Silicon plug



Hereby Assmann Electronic GmbH, declares that the Declaration of Conformity is part of the shipping content. If the Declaration of Conformity is missing, you can request it by post under the below mentioned manufacturer address.

#### www.assmann.com

Assmann Electronic GmbH Auf dem Schüffel 3 58513 Lüdenscheid Germany

