

Model	Lenovo TB-7104F
Model2	Tab E7
Type	Tablet
Partnumber	ZA400024SE
Ean	0192651071857
Country	SWEDEN
Warranty	2 YEAR



SPECIFICATION

Screen

Screen size inch	7
Screen size cm	17,65
Screen resolution	1024 x 600 pixels
Brightness	min: 250, typ: 300
Screen type	TN
Screen Features	SD,50% color gamut

Processor

Processor Model	MTK
Processor Number	MT8167 A/D
Processor Brand	MTK
Processor Architecture	32 BIT
Processor Series	4x ARM Cortex A35
Processor Clock Speed	1.3GHz
Number of CPU cores	Quad-core CPU
GPU graphic	IMG ge8300 500mhz

Memory (RAM)

Max memory installable (GB)	1GB
Memory installed (GB)	
Memory Speed	933MHz
Main memory type	LPDDR3

Storage

Max internal memory	16GB
Internal memory type	eMCP
Internal memory size	LP DDR3 1GB + 8GB

Media

Memory Card Reader	Micro SD
Max. Memory card space	128GB

Connectivity

WLAN	802.11 B/G/N+BT4.0
------	--------------------

Bluetooth version	4.0
Micro USB	1
USB 2.0	0
USB 3.0	0
USB C	0
NFC	0
Video interface - micro HDMI	No
Audio interface	3.5mm Audio Jack
Docking connector	No

SOUND

Sound	0
Speakers	1 x Front-Facing Speakers

FEATURES

Camera rear	2M FF Rear
Camera front	0.3M VGA
Video recording resolution	720P
Camera flash	No
Other features	No
Microphone	Single MIC
Keyboard	No
Keyboard language	
Pen	No
SIM card slot - Number	0
SIM card slot - Size	N/A
GPS	GPS+A-GPS
Tango GPS	No
Fingerprint reader	No
Enterprise pack	No

POWER

Battery type	Li-ion Polymer
Battery life	up to 20 hours
Battery Cells/Capacity	2750mAh
Power Supply Unit	5V 1A
	EU: Austria, Czech, Cyprus, Belgium, Bulgaria, Greek, Hungary, Iceland, Ireland, Israel, Finland,
Power plug area	France, Germany
100% Charging time	5h

GENERAL

Colour	SLATE BLACK
Case material	Plastic
RoHS	RoHS Compliant

Operating system	Android 8.0 Go Edition
------------------	------------------------



Operating system language	ENGLISH
Software included	No
Dimensions Net	193.2*110.54*10.35
Dimensions Gross	TBD
Weight Net	271.7±5g
Weight Gross	TBD