

**Industrial Ethernet
IE-FPOZ2EE0002DSJ0SJ0-X****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Assembled IE cables, FO patch cable, POF, SC-RJ - SC-RJ,
black

General ordering data

Type	IE-FPOZ2EE0002DSJ0SJ0-X
Order No.	1273430002
Version	Connecting line, PROFINET, SCRJ IP 20, SCRJ IP 20, 980 µm, 0.2 m
GTIN (EAN)	4050118467314
Qty.	1 pc(s).

Industrial Ethernet

IE-FPOZ2EE0002DSJ0SJ0-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	0.2 m	Length (inches)	0.008 inch
Net weight	0.01 g		

Temperatures

Operating temperature, max.	80 °C	Operating temperature, min.	-20 °C
Operating temperature	-20 °C...80 °C	Storage temperature	
Installation temperature			

Fibre-optic

Attenuation	≤ 160 dB/km at 650 nm	Bandwidth	≥ 100 MHz*km at 650 nm
Fibre type	POF	Insertion loss	≤ 1.0 dB

Cable structure

Core diameter	980 µm	Sheath diameter	2.2*4.5 mm
Cable layout	ZIPCORD	Insulation	PE
No. of wires	2	Sheathing colour	black

Mechanical and material properties of cable

Bending cycles	10.000	Min. bending radius, once only	25 mm
Min. bending radius, repetitive	25 mm	Pulling force	≤ 160 N
Halogen	No		

plug

Connector left	SCRJ IP 20	Connector right	SCRJ IP 20
----------------	------------	-----------------	------------

Classifications

ETIM 6.0	EC002599	eClass 6.2	27-06-10-03
eClass 9.0	27-06-03-08	eClass 9.1	27-06-03-08

Approvals

ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

Industrial Ethernet IE-FPOZ2EE0002DSJ0SJ0-X

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

Detailed drawing

